

Varistar CP Double Steel Door, Perforated With 3-Point Electronic Locking

Strømforsyning

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

FUNKSJONER

Double perforated steel door with 3-point locking for IP 20 protection class

Lever handle with push button, key

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with DIN profile half cylinder

SPESIFIKASJONER

Table 1/3

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-820	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-821	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-822	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-823	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-824	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-825	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3

Katalognummer	Finish	Locking Type	Materiell	Product Type	Protection Rating	Type
21630-820	Pulverlakkert	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-821	Pulverlakkert	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-822	Pulverlakkert	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-823	Pulverlakkert	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-824	Pulverlakkert	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated
21630-825	Pulverlakkert	3-Point Locking, Electronic	Stål	Cabinet Door	IP20	Steel Double Door, Perforated

Table 3/3

Katalognummer	Fungerer med
21630-820	Varistar CP
21630-821	Varistar CP
21630-822	Varistar CP
21630-823	Varistar CP
21630-824	Varistar CP
21630-825	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE