

Varistar CP Double Steel Door, Plain, 3-Point Locking

Strømforsyning

Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

FUNKSJONER

Double steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPESIFIKASJONER

Table 1/2						
Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-086	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-087	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-088	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-089	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-090	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-091	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-440	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-441	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-442	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-443	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-444	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-445	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-446	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-447	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Katalognummer	Locking Type	Product Type	Protection Rating	Type	Fungerer med
21630-086	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-087	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-088	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-089	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-090	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-091	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-440	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-441	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-442	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-443	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP

Katalognummer	Locking Type	Product Type	Protection Rating	Type	Fungerer med
21630-444	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-445	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-446	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP
21630-447	3-Point Locking	Cabinet Door	IP20	Steel Double Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE