

Varistar CP Perforated Door, Seismic IP20, Multi-Point Locking

Strømforsyning

IP 20 Seismic doors with reinforced and multi-point locking.

The multi-point locking helps achieve necessary contact to avoid EMI effects on electronics.

FUNKSJONER

Perforated door with Multi-Point locking for Seismic & IP 20 applications

Opening angle 180°

Lever handle with push button

SPESIFIKASJONER

Table 1/2

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-876	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-877	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-878	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-879	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-880	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-881	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2
21630-882	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-883	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2

Table 2/2

Katalognummer	Locking Type	Materiell	Product Type	Protection Rating	Type	Fungerer med
21630-876	4-Point Locking	Stål	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-877	4-Point Locking	Stål	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-878	4-Point Locking	Stål	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-879	4-Point Locking	Stål	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-880	4-Point Locking	Stål	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-881	4-Point Locking	Stål	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-882	5-Point Locking	Stål	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-883	5-Point Locking	Stål	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil.

Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE