

Varistar CP Plain Steel Door, Seismic EMC and IP55, Multi-Point Locking

Strømforsyning

EMC and IP55 Steel Door with lever handle and 4-Point locking.

FUNKSJONER

Lever handle with push button

Opening angle 180°

Steel door with Multi-Point locking for Seismic & EMC applications

SPESIFIKASJONER

Table 1/2

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-760	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-761	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-762	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-763	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-764	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-765	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-766	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529
21630-767	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-2, IEC 61587-3, IEC 60529

Table 2/2

Katalognummer	Locking Type	Materiell	Product Type	Protection Rating	Type	Fungerer med
21630-760	4-Point Locking	Stål	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-761	4-Point Locking	Stål	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-762	4-Point Locking	Stål	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-763	4-Point Locking	Stål	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-764	4-Point Locking	Stål	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-765	4-Point Locking	Stål	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-766	5-Point Locking	Stål	Cabinet Door	IP55	Steel Door, Plain	Varistar CP
21630-767	5-Point Locking	Stål	Cabinet Door	IP55	Steel Door, Plain	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk,

feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE