

Varistar CP Steel Door, Glazed With 3-Point Locking, Shortened

Strømforsyning

Shortened door available for IP20, IP55 applications.

FUNKSJONER

Glazed door

Height of connection plate 400mm

SPESIFIKASJONER

Table 1/2

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Locking Type
21630-346	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-342	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-345	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-344	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-347	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-343	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Katalognummer	Product Type	Protection Rating
21630-346	Cabinet Door	IP20

Katalognummer	Product Type	Protection Rating
21630-342	Cabinet Door	IP20
21630-345	Cabinet Door	IP20
21630-344	Cabinet Door	IP20
21630-347	Cabinet Door	IP20
21630-343	Cabinet Door	IP20

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE