

Varistar CP Steel Door, Perforated With 1-Point Locking

Strømforsyning

Varistar CP Perforated Steel Door Single Point Locking for IP 20 applications.

FUNKSJONER

Perforated steel door with single point locking for IP 20 protection class

Lever handle with built-in push button

Opening angle 180°

Key lock cover

SPESIFIKASJONER

Table 1/2

Katalognummer	Rack Height	Høyde	Bredde	Locking Type	Farge	Color Code
21630-408	24 U	1200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-409	24 U	1200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-507	24 U	1200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-508	24 U	1200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-410	29 U	1400 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-411	29 U	1400 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-509	29 U	1400 mm	600 mm	Single Point Locking	Black Grey	RAL 7021

Katalognummer	Rack Height	Høyde	Bredde	Locking Type	Farge	Color Code
21630-510	29 U	1400 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-412	33 U	1600 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-413	33 U	1600 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-511	33 U	1600 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-512	33 U	1600 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-414	38 U	1800 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-415	38 U	1800 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-513	38 U	1800 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-514	38 U	1800 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-006	42 U	2000 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-013	42 U	2000 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-515	42 U	2000 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-516	42 U	2000 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-007	47 U	2200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-014	47 U	2200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-517	47 U	2200 mm	600 mm	Single Point Locking	Black Grey	RAL 7021
21630-518	47 U	2200 mm	800 mm	Single Point Locking	Black Grey	RAL 7021
21630-008	52 U	2450 mm	600 mm	Single Point Locking	Black Grey	RAL 7021

Katalognummer	Rack Height	Høyde	Bredde	Locking Type	Farge	Color Code
21630-015	52 U	2450 mm	800 mm	Single Point Locking	Black Grey	RAL 7021

Table 2/2

Katalognummer	Samsvarer med	Product Type	Protection Rating	Type	Fungerer med
21630-408	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-409	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-507	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-508	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-410	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-411	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-509	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-510	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-412	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-413	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-511	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-512	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-414	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-415	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-513	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-514	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

Katalognummer	Samsvarer med	Product Type	Protection Rating	Type	Fungerer med
21630-006	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-013	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-515	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-516	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-007	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-014	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-517	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-518	IEC 61587-1	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-008	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP
21630-015	IEC 61587-1, IEC 61587-3	Cabinet Door	IP20	Steel Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order lever handle and DIN profile half cylinder separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlatelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE