

Varistar CP Steel Door, Plain With 3-Point Locking, IP20

Strømforsyning

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FUNKSJONER

Steel door with three point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

SPESIFIKASJONER

Table 1/2

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-104	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-105	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-106	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-107	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-108	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-109	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-432	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-433	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-434	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-435	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-436	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-437	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-438	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-439	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Katalognummer	Locking Type	Product Type	Protection Rating	Type	Fungerer med
21630-104	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-105	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-106	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-107	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-108	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-109	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-432	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-433	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-434	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-435	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP

Katalognummer	Locking Type	Product Type	Protection Rating	Type	Fungerer med
21630-436	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-437	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-438	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP
21630-439	3-Point Locking	Cabinet Door	IP20	Steel Door	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE