

Varistar CP Steel Door, Plain With 3-Point Locking, IP55

Strømforsyning

Steel door with mounting frame on inside, 3 point locking and with Lever handle with built-in push button.

FUNKSJONER

Steel door with three point locking for IP 55 protection class

Lever handle with built-in push button

Opening angle 180°

SPESIFIKASJONER

Table 1/3

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-171	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-210	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-211	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-212	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-213	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-214	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-215	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1
21630-216	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Katalognummer	Rack Height	Høyde	Bredde	Farge	Color Code	Samsvarer med
21630-217	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-218	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-219	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1
21630-220	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1

Table 2/3						
Katalognummer	Finish	Locking Type	Materiell	Product Type	Protection Rating	Type
21630-171	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-210	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-211	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-212	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-213	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-214	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-215	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-216	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-217	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-218	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-219	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door
21630-220	Pulverlakkert	3-Point Locking	Stål	Cabinet Door	IP55	Steel Door

Table 3/3

Katalognummer	Fungerer med
21630-171	Varistar CP
21630-210	Varistar CP
21630-211	Varistar CP
21630-212	Varistar CP
21630-213	Varistar CP
21630-214	Varistar CP
21630-215	Varistar CP
21630-216	Varistar CP
21630-217	Varistar CP
21630-218	Varistar CP
21630-219	Varistar CP
21630-220	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle separately.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter skal kun installeres og brukes som angitt i nVents produktinstruksjonsark og opplæringsmaterieil. Instruksjonsark er tilgjengelige på www.nvent.com og fra nVent-kundeservicerepresentanten din. Feil installasjon, misbruk, feil bruk eller annen unnlattelse av å følge nVents instruksjoner og advarsler i deres helhet kan forårsake produktfeil, skade på eiendom, alvorlig personskade og død og/eller ugyldiggjøre garantien din.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE