

Varistar CP Swing Frame for 600 mm Width

Power Utilities

The 19" swing frame allows the installation of sub-racks while simultaneously making wiring at the rear accessible.

Varistar CP swing frame comes with 150 KG load capacity, 120° movement and flexible pivot point.

FUNKSJONER

For full height or partial-height mounting

Pivot point can be selected right or left

Can accommodate 19" chassis and 19" subracks (maximum depth 200 mm)

120° hinge, square locks including 2 keys

Load-carrying capacity 150 kg

SPESIFIKASJONER

Table 1/2

Katalognummer	Rackhøyde	Farge	Fargekode	Høyde	Materiale	Produkttype
21630-668	24 U	Svart grå	RAL 7021	1200 mm	Stål	Skap/rackramme
21630-670	29 U	Svart grå	RAL 7021	1400 mm	Stål	Skap/rackramme
21630-672	33 U	Svart grå	RAL 7021	1600 mm	Stål	Skap/rackramme
21630-674	38 U	Svart grå	RAL 7021	1800 mm	Stål	Skap/rackramme
21630-676	42 U	Svart grå	RAL 7021	2000 mm	Stål	Skap/rackramme
21630-678	47 U	Svart grå	RAL 7021	2200 mm	Stål	Skap/rackramme

Table 2/2

Katalognummer	Beskyttelsesgrad	Bredde
21630-668	IP20	600 mm
21630-670	IP20	600 mm
21630-672	IP20	600 mm
21630-674	IP20	600 mm
21630-676	IP20	600 mm
21630-678	IP20	600 mm

YTTERLIGERE PRODUKTDETALJER

By aid of depth members 19" swing frames can be assembled directly on the cabinet frame or in depth-adjustable increments of 50 mm.

Please purchase the grounding kit separately.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE