

EuropacPRO Cover Plate for Horizontal Rail Type L, Light, 84 HP, 235 mm

KATALOGNUMMER

24561-052



Mechanical covering of installed components. The plate is inserted into a groove of the L type horizontal rails.

SERTIFISERINGER



FUNKSJONER

Mechanical covering of installed components

Suitable for "light" and "flexible" sub racks, for insertion into the groove of the light (type L) horizontal rails

Perforation ratio approx. 60%

PRODUKTEGENSKAPER

Rackbredde: 84HP

Dybde: 235mm

Antall pakker: 2

Materiale: Aluminium

Produktserie: EuropacPRO

Produkttype: Dekkplate

Type: Perforert

Fungerer med: Delrack

Pakkeenhet: Par

YTTERLIGERE PRODUKTDETALJER

Other dimensions on request.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE