

Bevegelsesdetektor

KATALOGNUMMER

60130-067



Bevegelsesdetektor: Klargjort for montering på dørkasse, deteksjonsmetode: Bevegelse, deteksjonsfelt av radar er justerbare, bredt felt 4 m (W) x 2 m (D), smalt felt 2 m (W) x 2,5 m (D), forsyningsspenning 12 ... 24 VAC eller 12? 30 VDC, strømforsyning via kontakt på dørplaten.

SERTIFISERINGER



FUNKSJONER

Nettspenning 12... 24 VAC eller 12? 30 VDC, strømforsyning via kontakt på dørplaten

Bredt felt 4 m (B) x 2 m (D)

Pilfelt 2 m (B) x 2,5 m (D)

Deteksjonsmetode: Bevegelse

Forberedt for montering på dørkasse

Deteksjonsfelt av radar er justerbare

PRODUKTEGENSKAPER

Produkttype: Sensor

Type: Bevegelsesdetektor

Arbeider med: Midtgang inneslutning

Net Weight: 0.508kg

Pakkeantall: 1

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE