

Intelligent iPDU, EN6450, 400 VAC, 3-PH, 16 A

KATALOGNUMMER

EN6450



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

FUNKSJONER

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

PRODUKTEGENSKAPER

Produktserie: Enlogic

Type: Intelligent PDU

Produkttype: Sokkelskinne

Kontakttype: (24) C13/C15; (24) C13/C15/C19/C21

Antall kontakter: 48

Farge: Svart

Kretsbyrter: Ingen kretsbyrter

Utganger med bryter: Ja

Kretsbytermengde: 0

Strømklassifisering: 11,5 kVA Nord-Amerika; 11,0 kVA internasjonal

Plassering av inngangskabel: Mating fra toppen

Maks. inngangseffekt: 11.5 / 11.0 kVA

Inngangsspenning: 380 – 415V

Fase: 3 PH

Av/på-bryter inkludert: Ja

Nominell spenning: 415V

Utgangsspenning: 208 – 230VAC

Pluggtype: IEC 60309 520P6/516P6

Strømstyrke (reduisert strømstyrke): 20 A (16 A) Nord-Amerika; 16 A, Internasjonal

Uttakbar inngangskabel: Nei

Rackenheter: 0U

Materiale: Stål

Overflate: Pulverbelagt

Målingstype: Utløp

Høyde: 1490mm

Bredde: 56mm

Dybde: 75mm

Vekt: 12kg

Antall pakker: 1

Lengde på inngangskabel: 1.8m

YTTERLIGERE PRODUKTDETALJER

Please order bracket for vertical mounting separately.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil,

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:

nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE