

# EuropacPRO 19" Subrack Kit for Backplane, Heavy, Retrofit Shielding, Front Handle

Non-EMC shielded subrack for backplane mounting, heavy version with tox welded side panels and front handle.



## SERTIFISERINGER



## FUNKSJONER

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Supplied as space-saving flat-pack

Rear horizontal rail for backplane mounting with insulation strip

Horizontal rail type "Heavy"

Shock and Vibration resistance up to 5 g

IP 20, in accordance with IEC 60529

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Installed load up to 15 kg

Version with front handles

## SPESIFIKASJONER

**Materiale:** Aluminium

**Overflate:** Anodisert; Passivert

**EMC-beskyttelse:** Nei  
**Produkttype:** Delrack/chassis

Table 1/3

| Katalognummer | Rackhøyde | Dybde | Antall pakker | For montering | Kortdybde                  | EMC-pakningstype |
|---------------|-----------|-------|---------------|---------------|----------------------------|------------------|
| 24567-161     | 3U        | 175mm | 1             | Sentralenhet  | 160mm                      | Rustfritt stål   |
| 24567-162     | 3U        | 235mm | 1             | Sentralenhet  | 160mm, 220mm               | Rustfritt stål   |
| 24567-163     | 3U        | 295mm | 1             | Sentralenhet  | 160mm, 220mm, 280mm        | Rustfritt stål   |
| 24567-164     | 3U        | 355mm | 1             | Sentralenhet  | 160mm, 220mm, 280mm, 340mm | Rustfritt stål   |
| 24567-461     | 6U        | 175mm | 1             | Sentralenhet  | 160mm                      | Rustfritt stål   |
| 24567-462     | 6U        | 235mm | 1             | Sentralenhet  | 160mm, 220mm               | Rustfritt stål   |
| 24567-463     | 6U        | 295mm | 1             | Sentralenhet  | 160mm, 220mm, 280mm        | Rustfritt stål   |
| 24567-464     | 6U        | 355mm | 1             | Sentralenhet  | 160mm, 220mm, 280mm, 340mm | Rustfritt stål   |

Table 2/3

| Katalognummer | Støt- og vibrasjonstoleranse | Håndtak inkludert | Montering | Samsvarer med   | Rackbredde | Statisk belastning |
|---------------|------------------------------|-------------------|-----------|-----------------|------------|--------------------|
| 24567-161     | 5g (force)                   | Ja                | Stativ    | IEC 60297-3-103 | 84HP       | 15kg               |
| 24567-162     | 5g (force)                   | Ja                | Stativ    | IEC 60297-3-103 | 84HP       | 15kg               |
| 24567-163     | 5g (force)                   | Ja                | Stativ    | IEC 60297-3-103 | 84HP       | 15kg               |
| 24567-164     | 5g (force)                   | Ja                | Stativ    | IEC 60297-3-103 | 84HP       | 15kg               |
| 24567-461     | 5g (force)                   | Ja                | Stativ    | IEC 60297-3-103 | 84HP       | 15kg               |

| Katalognummer | Støt- og vibrasjonstoleranse | Håndtak inkludert | Montering | Samsvarer med   | Rackbredde | Statisk belastning |
|---------------|------------------------------|-------------------|-----------|-----------------|------------|--------------------|
| 24567-462     | 5g (force)                   | Ja                | Stativ    | IEC 60297-3-103 | 84HP       | 15kg               |
| 24567-463     | 5g (force)                   | Ja                | Stativ    | IEC 60297-3-103 | 84HP       | 15kg               |
| 24567-464     | 5g (force)                   | Ja                | Stativ    | IEC 60297-3-103 | 84HP       | 15kg               |

Table 3/3

| Katalognummer | Sertifiseringer | Hurtiglevering |
|---------------|-----------------|----------------|
| 24567-161     | RoHS            | Nei            |
| 24567-162     | RoHS, DB        | Nei            |
| 24567-163     | DB, RoHS        | Nei            |
| 24567-164     | RoHS, DB        | Nei            |
| 24567-461     | DB, RoHS        | Nei            |
| 24567-462     | RoHS, DB        | Nei            |
| 24567-463     | RoHS, DB        | Nei            |
| 24567-464     | RoHS, DB        | Nei            |

## YTTERLIGERE PRODUKTDETALJER

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

## ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmaterieill. Instruksjonsark er tilgjengelig på [www.nvent.com](http://www.nvent.com) og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

#### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

#### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

#### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

#### Middle East & India

Dubai, United Arab  
Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



Vår solide portefølje av merkevarer:

**CADDY   ERICO   HOFFMAN   ILSCO   SCHROFF   TRACHTE**