

EuropacPRO 19" Subrack Kit for Backplane, Light, Unshielded

Non-EMC shielded subrack for backplane mounting, light version.



SERTIFISERINGER



FUNKSJONER

Subrack with side panel type L ("light") with integrated 19" support brackets

Horizontal rail type "light"

Aluminum construction

Rear horizontal rails for backplane mounting with insulation strip

Installed load up to 7.5 kg

Supplied as space-saving flat-pack

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Modifications such as cutouts, different finishes or dimensions available

SPESIFIKASJONER

Materiale:	Aluminium
Overflate:	Anodisert; Passivert
EMC-beskyttelse:	Nei
Produkttype:	Delrack/chassis

Table 1/2

Katalognummer	Rackhøyde	Dybde	Antall pakker	For montering	Kortdybde	Håndtak inkludert
24564-131	3U	175mm	1	Sentralenhet	160mm	Nei
24564-132	3U	235mm	1	Sentralenhet	160mm, 220mm	Nei
24564-133	3U	295mm	1	Sentralenhet	160mm, 220mm, 280mm	Nei
24564-431	6U	175mm	1	Sentralenhet	160mm	Nei
24564-432	6U	235mm	1	Sentralenhet	160mm, 220mm	Nei
24564-433	6U	295mm	1	Sentralenhet	160mm, 220mm, 280mm	Nei

Table 2/2

Katalognummer	Montering	Samsvarer med	Rackbredde	Statisk belastning	Hurtiglevering
24564-131	Stativ	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	84HP	7.5kg	Nei
24564-132	Stativ	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	84HP	7.5kg	Nei
24564-133	Stativ	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	84HP	7.5kg	Nei
24564-431	Stativ	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	84HP	7.5kg	Nei
24564-432	Stativ	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	84HP	7.5kg	Nei
24564-433	Stativ	IEC 60297-3-100, IEC 60297-3-101, IEEE 1101,1	84HP	7.5kg	Nei

YTTERLIGERE PRODUKTDETALJER

Subrack is not prepared for shielding, retrofit for protection class IP 20 possible

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE