

EuropacPRO Advanced EMC Side Panel Covers for C-Profile Adaptors



Aluminium Side panel 3 mm to increase the EMC shielding effect of the subrack by increasing the material thickness and covering the not needed cut-outs. In this version specially prepared for the installation of an adapter for fixing the subrack with C-profile telescopic slides in a cabinet.

FUNKSJONER

Side panel covers for increased lateral RF shielding, specially prepared for the installation of an adapter for fixing the subrack with C-profile telescopic slides in a cabinet

Assembled on the outside of the standard side panel

Assembly material included

Compatible C-profile adaptors can be found in the recommended accessory section

SPESIFIKASJONER

Table 1/2

Katalognummer	Produkttype	Produktserie	Type	Rackhøyde	Dybde	EMC-beskyttelse
24563-355	Sidepanel	EuropacPRO	Type H	3U	175mm	Ja
24563-356	Sidepanel	EuropacPRO	Type H	3U	235mm	Ja
24563-359	Sidepanel	EuropacPRO	Type H	3U	295mm	Ja
24563-360	Sidepanel	EuropacPRO	Type H	3U	355mm	Ja
24563-361	Sidepanel	EuropacPRO	Type H	3U	415mm	Ja
24563-362	Sidepanel	EuropacPRO	Type H	3U	495mm	Ja
24563-375	Sidepanel	EuropacPRO	Type H	6U	175mm	Ja

Katalognummer	Produkttype	Produktserie	Type	Rackhøyde	Dybde	EMC-beskyttelse
24563-376	Sidepanel	EuropacPRO	Type H	6U	235mm	Ja
24563-379	Sidepanel	EuropacPRO	Type H	6U	295mm	Ja
24563-380	Sidepanel	EuropacPRO	Type H	6U	355mm	Ja
24563-381	Sidepanel	EuropacPRO	Type H	6U	415mm	Ja
24563-382	Sidepanel	EuropacPRO	Type H	6U	495mm	Ja

Table 2/2

Katalognummer	Lengde	Materiale	Overflate	Antall pakker	Pakkeenhet	Hurtiglevering
24563-355	175mm	Aluminium	Passivert	2	Par	Nei
24563-356	235mm	Aluminium	Passivert	2	Par	Nei
24563-359	295mm	Aluminium	Passivert	2	Par	Nei
24563-360	355mm	Aluminium	Passivert	2	Par	Nei
24563-361	415mm	Aluminium	Passivert	2	Par	Nei
24563-362	495mm	Aluminium	Passivert	2	Par	Nei
24563-375	175mm	Aluminium	Passivert	2	Par	Nei
24563-376	235mm	Aluminium	Passivert	2	Par	Nei
24563-379	295mm	Aluminium	Passivert	2	Par	Nei
24563-380	355mm	Aluminium	Passivert	2	Par	Nei
24563-381	415mm	Aluminium	Passivert	2	Par	Nei

Katalognummer	Lengde	Materiale	Overflate	Antall pakker	Pakkeenhet	Hurtiglevering
24563-382	495mm	Aluminium	Passivert	2	Par	Nei

YTTERLIGERE PRODUKTDETALJER

Side panel and 19" bracket are tox-cold welded together. toxen = Clinching technique, without add aids. This takes place with special tools and high pressure.

Versions besides 3 and 6 U available on request.

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE