

Frontpanel, monter skjerming



Flatt frontpanel. Skivbar med EMC-pakning i rustfritt stål.

SERTIFISERINGER



FUNKSJONER

For EMC-pakning i rustfritt stål

Al, 2,5 mm, front anodisert, ledende

SPESIFIKASJONER

Dybde (D):	2.5mm
Materiale:	Aluminium
Tilbehørstype:	Frontpanel
Produkttype:	Frontpanel
Type:	Frontpanel uten håndtak
EMC-skjerming:	Nei (ettermonterbar)

Table 1/3

Katalognummer	Rackhøyde	Rackbredde	Pakkeantall	Montering	Pakning	Front finish
20846-425	3U	3HP	1	Skrue foran	Rustfritt stål EMC	Eloksert

Katalognummer	Rackhøyde	Rackbredde	Pakkeantall	Montering	Pakning	Front finish
30846-865	6U	2HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-426	3U	4HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-427	3U	5HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-428	3U	6HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-429	3U	7HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-443	6U	4HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-430	3U	8HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-442	6U	3HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-431	3U	10HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-444	6U	5HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-432	3U	12HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-445	6U	6HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-433	3U	14HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-446	6U	7HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-424	3U	16HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-447	6U	8HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-448	6U	10HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-434	3U	21HP	1	Skrue foran	Rustfritt stål EMC	Eloksert

Katalognummer	Rackhøyde	Rackbredde	Pakkeantall	Montering	Pakning	Front finish
20846-449	6U	12HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-436	3U	28HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-450	6U	14HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-456	6U	16HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-451	6U	21HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-437	3U	42HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
30846-588	2U	84HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-452	6U	28HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-438	3U	63HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
30846-676	3U	84HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-453	6U	42HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
30846-683	4U	84HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
20846-454	6U	63HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
30846-771	6U	84HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
30846-859	9U	84HP	1	Skrue foran	Rustfritt stål EMC	Eloksert
30846-864	3U	2HP	1	Skrue foran	Rustfritt stål EMC	Eloksert

Table 2/3

Katalognummer	Bakutførelse	Behandlede kanter	Samsvarer med	Avslutt	Høyde (H)	Bredde (W)
---------------	--------------	-------------------	---------------	---------	-----------	------------

20846-425	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	14.9mm
30846-865	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	9.8mm
20846-426	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	20mm
20846-427	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	25mm
20846-428	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	30.1mm
20846-429	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	35.2mm
20846-443	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	20mm
20846-430	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	40.3mm
20846-442	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	14.9mm
20846-431	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	50.5mm
20846-444	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	25mm
20846-432	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	60.6mm
20846-445	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	30.1mm
20846-433	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	70.8mm
20846-446	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	35.2mm

20846-424	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	80.9mm
20846-447	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	40.3mm
20846-448	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	50.5mm
20846-434	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	106.3mm
20846-449	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	60.6mm
20846-436	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	141.9mm
20846-450	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	70.8mm
20846-456	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	80.9mm
20846-451	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	106.3mm
20846-437	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	213mm
30846-588	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert, Passivisert	84mm	426.4mm
20846-452	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	141.9mm
20846-438	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	319.7mm
30846-676	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert, Passivisert	128.4mm	426.4mm
20846-453	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	213mm

30846-683	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	172.9mm	426.4mm
20846-454	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	319.7mm
30846-771	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	261.8mm	426.4mm
30846-859	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	395.1mm	426.4mm
30846-864	Ledende	Nei	IEC 60297-3-101, IEEE 1101.1/10	Eloksert	128.4mm	9.8mm

Table 3/3

Katalognummer	Hurtiglevering
20846-425	Nei
30846-865	Nei
20846-426	Nei
20846-427	Nei
20846-428	Nei
20846-429	Nei
20846-443	Nei
20846-430	Nei
20846-442	Nei
20846-431	Nei
20846-444	Nei

Katalognummer	Hurtiglevering
20846-432	Nei
20846-445	Nei
20846-433	Nei
20846-446	Nei
20846-424	Nei
20846-447	Nei
20846-448	Nei
20846-434	Nei
20846-449	Nei
20846-436	Nei
20846-450	Nei
20846-456	Nei
20846-451	Nei
20846-437	Nei
30846-588	Nei
20846-452	Nei
20846-438	Nei
30846-676	Nei

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE