

PropacPRO Complete Desktop Case, Unshielded



The nVent SCHROFF PropacPRO case provides electronics protection for 19" assemblies such as plug-in units and euroboards. The aluminum die cast frames and profile sidepanels guarantee a robust solution. In addition an extensive accessory range is available.

SERTIFISERINGER



FUNKSJONER

Desktop case, pre-configured in accordance with IEC 60297-3-101 for 19" components

Unshielded

Ventilation slots in base plate

Rear panel perforated

Conforms with DIN EN 62368-1

SPESIFIKASJONER

Statisk belastning:	25kg
Produkttype:	Eske
Type:	Eske for 19-tommers komponenter
EMC-beskyttelse:	Nei (kan monteres etterpå)
Produktserie:	PropacPRO

Table 1/3

Katalognummer	Rackhøyde	Rackbredde	Dybde	Antall pakker	Høyde som kan brukes	Bredde som kan brukes
24576-001	3U	28HP	266mm	1	112.3mm	148mm
24576-002	3U	28HP	326mm	1	112.3mm	148mm
24576-003	3U	42HP	266mm	1	112.3mm	219mm
24576-004	3U	42HP	326mm	1	112.3mm	219mm
24576-005	3U	42HP	386mm	1	112.3mm	219mm
24576-006	3U	63HP	266mm	1	112.3mm	326mm
24576-007	3U	63HP	326mm	1	112.3mm	326mm
24576-008	3U	63HP	386mm	1	112.3mm	326mm
24576-009	3U	84HP	266mm	1	112.3mm	432mm
24576-010	3U	84HP	326mm	1	112.3mm	432mm
24576-011	3U	84HP	386mm	1	112.3mm	432mm
24576-012	3U	84HP	446mm	1	112.3mm	432mm
24576-013	3U	84HP	506mm	1	112.3mm	432mm
24576-021	6U	84HP	326mm	1	245.7mm	432mm
24576-022	6U	84HP	446mm	1	245.7mm	432mm

Table 2/3

Katalognummer	Fremre ramme	Kjølealternativ	Samsvarer med	Overflate	Høyde	Materiale
24576-001	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium

Katalognummer	Fremre ramme	Kjølealternativ	Samsvarer med	Overflate	Høyde	Materiale
24576-002	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-003	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-004	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-005	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-006	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-007	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-008	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-009	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-010	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-011	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-012	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-013	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	155.5mm	Aluminium
24576-021	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	289mm	Aluminium
24576-022	Ett stykke	Nei	IEC 60297-3-101	Passivert, Pulverbelagt	289mm	Aluminium

Table 3/3

Katalognummer	Beskyttelsesgrad	Bredde	Hurtiglevering
24576-001	IP20	185.9mm	Nei
24576-002	IP20	185.9mm	Nei
24576-003	IP20	257mm	Nei

Katalognummer	Beskyttelsesgrad	Bredde	Hurtiglevering
24576-004	IP20	257mm	Nei
24576-005	IP20	257mm	Nei
24576-006	IP20	363.7mm	Nei
24576-007	IP20	363.7mm	Nei
24576-008	IP20	363.7mm	Nei
24576-009	IP20	470.3mm	Nei
24576-010	IP20	470.3mm	Nei
24576-011	IP20	470.3mm	Nei
24576-012	IP20	470.3mm	Nei
24576-013	IP20	470.3mm	Nei
24576-021	IP20	470.3mm	Nei
24576-022	IP20	470.3mm	Nei

ADVARSEL

nVent-produkter må installeres og brukes bare som beskrevet i nVent sine instruksjonsark og opplæringsmateriell. Instruksjonsark er tilgjengelig på www.nvent.com og fra din nVent kundeservice-representant. Ukorrekt installasjon, misbruk, feilaktig anvendelse eller annen manglende etterlevelse av nVent sine instruksjoner og advarsler kan føre til produktfeil, skade på eiendom, alvorlige personskader og død og/eller gjøre garantien ugyldig.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



Vår solide portefølje av merkevarer:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE