


Wzmocniona, odchylana rama szafy typu Rack



Heavy-Duty Swing-Out Rack Frame allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Mounting supports and swing-out frame can be located deeper into the frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame. Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.

FUNKCJE

Swing-out mounting supports mount to inside of frame at any vertical location; flexibility to select any model size equal to or shorter in height (i.e. use of 1400mm rack frame in 2000mm high enclosure)

Spring-loaded pivot post makes installation easy

Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames

Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Furnished with hinges, two quarter-turn latches and mounting hardware

Complies with ANSI/EIA RS-310-D rack-mounting standards

Maximum equipment load is 300 lb. (136 kg)

Mounting holes accommodate either English or metric cage nuts, which are ordered separately

Swing-Out Rack Frame assemblies are supplied with mounting supports

Hinges that provide 170-degree rotation are optional

RAL 7035 textured light-gray polyester powder paint

SPECYFIKACJE

Grubość: 2.66mm
Kolor: Jasnoszary
Zakończ: Malowany proszkowo
Kod koloru: RAL 7035

Table 1/1

Numer katalogowy	Materiał	Pasuje do szerokości ramy	Jednostki stelaża	Szybka wysyłka
PSF76	Stal miękka	600mm	10U	Nie
PSF146	Stal miękka	600mm	25U	Nie
PSF148	Stal miękka	800mm	25U	Nie
PSF78	Stal miękka	800mm	10U	Nie
PSF168	Stal miękka	800mm	30U	Nie
PSF186	Stal miękka	600mm	34U	Nie
PSF188	Stal miękka	800mm	34U	Nie
PSF206	Stal miękka	600mm	39U	Nie
PSF77	Stal miękka	700mm	10U	Nie
PSF207	Stal miękka	700mm	39U	Nie
PSF208	Stal miękka	800mm	39U	Nie
PSF226	Stal miękka	600mm	43U	Nie
PSF227	Stal miękka	700mm	43U	Nie
PSF228	Stal miękka	800mm	43U	Nie
PSF166	Stal miękka	600mm	30U	Nie

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Marki w naszej ofercie:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE