

# ProLine Heavy-Duty Swing-Out Rack Frame



Heavy-Duty Swing-Out Rack Frame allows 19-in. rack equipment to pivot out of the enclosure frame for better accessibility. The frames mount on hinges capable of 120-degree rotation. Mounting supports and swing-out frame can be located deeper into the frame using grid system straps. Deeper mounting affects the degree of opening of swing-out frame. Mounting supports for an 800-mm wide enclosure frame permit you to either center the rack-mounting frame or position it right or left. The frame can also pivot from either the left or the right for maximum flexibility.

## FUNKCJE

Swing-out mounting supports mount to inside of frame at any vertical location; flexibility to select any model size equal to or shorter in height (i.e. use of 1400mm rack frame in 2000mm high enclosure)

Spring-loaded pivot post makes installation easy

Rack Frames are available for 600-, 700- and 800-mm wide enclosure frames

Swing-Out Rack Frames can also be installed in right, left or both bays of 1200-mm wide frames using center uprights

Furnished with hinges, two quarter-turn latches and mounting hardware

Complies with ANSI/EIA RS-310-D rack-mounting standards

Maximum equipment load is 300 lb. (136 kg)

Mounting holes accommodate either English or metric cage nuts, which are ordered separately

Swing-Out Rack Frame assemblies are supplied with mounting supports

Hinges that provide 170-degree rotation are optional

RAL 7035 textured light-gray polyester powder paint

## SPECYFIKACJE

| Table 1/1        |             |            |            |                   |         |                |
|------------------|-------------|------------|------------|-------------------|---------|----------------|
| Numer katalogowy | Materiał    | Kolor      | Kod koloru | Wykończenie       | Grubość | Szybka wysyłka |
| PSF187           | Stal miękka | Jasnoszary | RAL 7035   | Powłoka proszkowa | 2.66mm  | Nie            |

## OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie [www.nvent.com](http://www.nvent.com) oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Marki w naszej ofercie:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE