

Modular Single Door, MCSS-HP

Instalacje zasilające



The stainless steel single door modular floor standing enclosure range, MCSS-HP, with a IP 66 protection degree offers a higher protection level for equipment and components which will help extend their lifetime and reduce maintenance costs when the enclosure is installed for rough environments with severe conditions. These new enclosures are rated as IP66 even if they are bayed between them using the standard baying brackets.

INDUSTRY STANDARDS

NEMA Type 4X, 12, 13

IP66

IK10

FUNKCJE

Frame: Seam welded reversed open profiles with 25 mm hole pattern, according to DIN 43660 including integrated external hole pattern

Door: Mounted with four hinges, allowing left or right hand opening; ncluding door frame with 25 mm hole pattern

Rear panel: Fitted by M6 torx screws; standard facilities for rear door mounting

Supplied as an accessory

Removable roof panel

Lock: Espagnolette 4-point locking system which does not interfere with the enclosure inner space; standard double-bit lock with 3 mm insert

Bottom plate: One piece bottom plate, with injected polyurethane gasket to ensure maximum sealing

Mounting plate: Double folded and slides into position with adjustable depths of 25 mm, with the MPD02 accessory

Earthing/Grounding: All panels are earthed/grounded through their fittings and equipped with a separate earthing stud

Mounting requirements: For stand-alone installation, add side panels; for combined installation, HPPG01 and baying brackets, CCI and CCM are required

Delivery: Frame with fitted door, rear panel, roof panel, bottom plate, mounting plate and door frame; delivery also includes earthing bolts

OKREŚLENIU SPECYFIKACJI

Table 1/2

Numer katalogowy	Numer artykułu	Wysokość	Szerokość	Głębokość	Materiał	Wykończenie
MCSS20086HP	MCSS20086HP	2000 mm	800 mm	600 mm	Stal nierdzewna	Brushed

Table 2/2

Numer katalogowy	Numer artykułu	Kolor	Body Thickness	Door Thickness
MCSS20086HP	MCSS20086HP	Unpainted	1.5 mm	2 mm

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE