

MultipacPRO 19" Chassis, Aluminum, Plain Top and Base

Instalacje zasilające



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version have plain top and bottom cover.

CERTYFIKATY



FUNKCJE

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

OKREŚLENIU SPECYFIKACJI

Table 1/2

Numer katalogowy	Rack Height	Głębokość	Usable Width	Montaż	Zgodność z	EMC Shielding
20860-601	1 U	220 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-602	1 U	280 mm	403 mm	Rack	IEC 60297-3-100, IEC 60297-3-105	No (Retrofittable)
20860-603	1 U	340 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-604	2 U	220 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-605	2 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-606	2 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-607	3 U	280 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-608	3 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-609	3 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-610	3 U	460 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-611	4 U	280 mm	4 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-612	4 U	340 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-613	4 U	400 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-614	4 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)
20860-615	5 U	460 mm	403 mm	Rack	IEC 60297-3-100	No (Retrofittable)

Table 2/2

Numer katalogowy	Product Family	Product Type	Typ	Certyfikaty
20860-601	MultipacPRO	Subrack/Chassis	Lity	RoHS

Numer katalogowy	Product Family	Product Type	Typ	Certyfikaty
20860-602	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-603	MultipacPRO	Subrack/Chassis	Lity	
20860-604	MultipacPRO	Subrack/Chassis	Lity	
20860-605	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-606	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-607	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-608	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-609	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-610	MultipacPRO	Subrack/Chassis	Lity	
20860-611	MultipacPRO	Subrack/Chassis	Lity	
20860-612	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-613	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-614	MultipacPRO	Subrack/Chassis	Lity	RoHS
20860-615	MultipacPRO	Subrack/Chassis	Lity	RoHS

ADDITIONAL PRODUCT DETAILS

Please order front handles separately.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE