

Novastar Cabinet With Glazed Door and Rear Panel

Instalacje zasilające



Aluminum frame cabinets with attractive design, ideally suited for general electronics, test and measurement, audio/video and broadcasting applications.

CERTYFIKATY



FUNKCJE

Type of protection IP 20

Cabinet width only 553 mm

Flush cladding parts

All uprights (front and rear) with 19" cut-outs

Bolted, die-cast frame with Al extrusions

With glass door (smoke grey) and rear panel

OKREŚLENIU SPECYFIKACJI

Table 1/3

Numer katalogowy	Rack Height	Frame Color	Wysokość	Frame Color Code	Cladding Material	Szerokość
------------------	-------------	-------------	----------	------------------	-------------------	-----------

15230-019	12 U	Black Grey	589 mm	RAL 7021	Stal	553 mm
16230-019	12 U	Black Grey	589 mm	RAL 7021	Stal	553 mm
15230-020	16 U	Black Grey	767 mm	RAL 7021	Stal	553 mm
16230-020	16 U	Black Grey	767 mm	RAL 7021	Stal	553 mm
15230-021	20 U	Black Grey	945 mm	RAL 7021	Stal	553 mm
16230-021	20 U	Black Grey	945 mm	RAL 7021	Stal	553 mm
15230-022	38 U	Black Grey	1745 mm	RAL 7021	Stal	553 mm
15230-023	38 U	Black Grey	1745 mm	RAL 7021	Stal	553 mm
16230-022	38 U	Black Grey	1745 mm	RAL 7021	Stal	553 mm
16230-023	38 U	Black Grey	1745 mm	RAL 7021	Stal	553 mm
15230-024	43 U	Black Grey	1967 mm	RAL 7021	Stal	553 mm
15230-025	43 U	Black Grey	1967 mm	RAL 7021	Stal	553 mm
16230-024	43 U	Black Grey	1967 mm	RAL 7021	Stal	553 mm
16230-025	43 U	Black Grey	1967 mm	RAL 7021	Stal	553 mm

Table 2/3

Numer katalogowy	Cladding Color	Głębokość	Obciążenie statyczne	Cladding Color Code	Zgodność z	Frame Material
15230-019	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-019	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-020	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium

Numer katalogowy	Cladding Color	Głębokość	Obciążenie statyczne	Cladding Color Code	Zgodność z	Frame Material
16230-020	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-021	Black Grey	600 mm	200 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-021	Light Grey	600 mm	200 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-022	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
15230-023	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-022	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
16230-023	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
15230-024	Black Grey	600 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
15230-025	Black Grey	800 mm	400 kgf	RAL 7021	IEC 60529, IEC 60297-3-100	Aluminium
16230-024	Light Grey	600 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium
16230-025	Light Grey	800 mm	400 kgf	RAL 7035	IEC 60529, IEC 60297-3-100	Aluminium

Table 3/3

Numer katalogowy	Product Type	Protection Rating
15230-019	Cabinet	IP20
16230-019	Cabinet	IP20
15230-020	Cabinet	IP20
16230-020	Cabinet	IP20
15230-021	Cabinet	IP20
16230-021	Cabinet	IP20

Numer katalogowy	Product Type	Protection Rating
15230-022	Cabinet	IP20
15230-023	Cabinet	IP20
16230-022	Cabinet	IP20
16230-023	Cabinet	IP20
15230-024	Cabinet	IP20
15230-025	Cabinet	IP20
16230-024	Cabinet	IP20
16230-025	Cabinet	IP20

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE