

RackPower Basic PDU, RB0xxx, 230 VAC, 1-phase

Instalacje zasilające

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 and C19 outlets.

FUNKCJE

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200 - 240 VAC, 1-phase L-N

Input connector IEC 60309 332P6

C13 and C19 outlets

1RU aluminum profile

Adjustable Toolless Mounting

OKREŚLENIU SPECYFIKACJI

Table 1/2

Numer katalogowy	Product Type	Socket Type	Kolor	Długość	Voltage AC	Głębokość
RB0328	Socket Strip	IEC C13, IEC C19	Czarny	1490 mm	230 V	53 mm

Table 2/2

Numer katalogowy	Szerokość
RB0328	52 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE