

RackPower Basic PDU, RB0xxx, 230/400 VAC, 3-phase

Instalacje zasilające

Modular, compact PDU. Using a 1 U aluminum chassis the PDU can easily be integrated in a rack with C13 / C19 Combo outlets.

FUNKCJE

RackPower Basic Power Distribution Units enable power in Cabinets as well as Open Frame Racks and Wall-Mount enclosures

Input Voltage Range 200-240/346-415VAC, 3-phase WYE

Connecting cable 6", with IEC 60309 3P+N+E connector

C13 and C13/C19 Combo outlets

1RU aluminum profile

Adjustable Toolless Mounting

OKREŚLENIU SPECYFIKACJI

Table 1/2

Numer katalogowy	Product Type	Socket Type	Kolor	Długość	Voltage AC	Głębokość
RB0450	Socket Strip	IEC C13, IEC C13/C19	Czarny	1490 mm	230 V	55 mm
RB0850	Socket Strip	IEC C13, IEC C13/C19	Czarny	1780 mm	230 V	55 mm

Table 2/2

Numer katalogowy	Szerokość
RB0450	56 mm
RB0850	56 mm

ADDITIONAL PRODUCT DETAILS

Please order bracket for vertical mounting separately.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE