

RatiopacPRO 19" Rack Mount Case, Retrofittable Shielding With Handles

Instalacje zasilające



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides mounting brackets and handles for assembly into a 19" rack.

CERTYFIKATY



FUNKCJE

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Version with 19" mounting brackets with front handles

Retrofittable EMC shielding

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

No visible screws; cladding parts removable without tools

Symmetrical design, identical front and rear side

Conforms with DIN EN 62368-1

OKREŚLENIU SPECYFIKACJI

Table 1/3

Numer katalogowy	Rack Height	Głębokość	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-620	2 U	255.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-623	2 U	315.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-624	2 U	375.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-625	2 U	435.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-626	2 U	495.5 mm	1	67.9 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-630	3 U	255.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-633	3 U	315.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-634	3 U	375.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-635	3 U	435.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-636	3 U	495.5 mm	1	112.3 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-640	4 U	255.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails

Numer katalogowy	Rack Height	Głębokość	Package Quantity	Usable Height	Usable Width	Front Frame Construction
24572-643	4 U	315.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-644	4 U	375.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-645	4 U	435.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-646	4 U	495.5 mm	1	156.8 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-660	6 U	255.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-663	6 U	315.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-664	6 U	375.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-665	6 U	435.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-666	6 U	495.5 mm	1	245.7 mm	432 mm	19" Mounting Brackets with Handles, Horizontal Rails

Table 2/3

Numer katalogowy	Cooling Option	Zgodność z	EMC Shielding	Wysokość	Product Family	Product Type
------------------	----------------	------------	---------------	----------	----------------	--------------

24572-620	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-623	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-624	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-625	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-626	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	88.1 mm	RatiopacPRO	Case
24572-630	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24572-633	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24572-634	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case

24572-635	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24572-636	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	132.6 mm	RatiopacPRO	Case
24572-640	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-643	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-644	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-645	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-646	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	177 mm	RatiopacPRO	Case
24572-660	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case

24572-663	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24572-664	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24572-665	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case
24572-666	Nie	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	No (Retrofittable)	265.9 mm	RatiopacPRO	Case

Table 3/3

Numer katalogowy	Protection Rating	Rack Width	Obciążenie statyczne	Typ	Szerokość
24572-620	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-623	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-624	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-625	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-626	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-630	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

Numer katalogowy	Protection Rating	Rack Width	Obciążenie statyczne	Typ	Szerokość
24572-633	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-634	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-635	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-636	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-640	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-643	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-644	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-645	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-646	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-660	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-663	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-664	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-665	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm
24572-666	IP20	84 HP	25 kgf	Case for Individual Electronic Components	448.9 mm

ADDITIONAL PRODUCT DETAILS

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE