

Varistar CP Double Steel Door, Perforated, 3-Point Locking

Instalacje zasilające

Perforated Varistar CP steel double door with 3-point locking and 2 door hinges for applications with IP 20 protection.

FUNKCJE

Double perforated steel door with 3 point locking for IP 20 protection class

Lever handle with key insert (2 keys)

Opening angle 180°

Standard fitting, lock on right-hand door

Can be retrofitted with lever handle 24630003 and DIN profile half cylinder with keys or push button

OKREŚLENIU SPECYFIKACJI

Table 1/2

Numer katalogowy	Rack Height	Wysokość	Szerokość	Kolor	Color Code	Zgodność z
21630-020	42 U	2000 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-021	47 U	2200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-022	52 U	2450 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-027	42 U	2000 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-028	47 U	2200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-029	52 U	2450 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-448	24 U	1200 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Numer katalogowy	Rack Height	Wysokość	Szerokość	Kolor	Color Code	Zgodność z
21630-449	24 U	1200 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-450	29 U	1400 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-451	29 U	1400 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-452	33 U	1600 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-453	33 U	1600 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-454	38 U	1800 mm	600 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3
21630-455	38 U	1800 mm	800 mm	Black Grey	RAL 7021	IEC 61587-1, IEC 61587-3

Table 2/2

Numer katalogowy	Locking Type	Product Type	Protection Rating	Typ	Works With
21630-020	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-021	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-022	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-027	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-028	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-029	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-448	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-449	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-450	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-451	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP

Numer katalogowy	Locking Type	Product Type	Protection Rating	Typ	Works With
21630-452	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-453	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-454	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP
21630-455	3-Point Locking	Cabinet Door	IP20	Steel Double Door, Perforated	Varistar CP

ADDITIONAL PRODUCT DETAILS

Please order DIN profile half cylinder for lever handle 24630003 separately.

Please purchase the grounding kit separately.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE