

Varistar CP IP 20 Cabinet, Glass Front Door, Steel Rear Door

Instalacje zasilające

Varistar: Highly versatile, robust welded steel frame electronics cabinet with a wide range of available features including protection against dust and water (IP 20 and IP 55), cooling options from fans to 40kW air-to-water chillers, shock, vibration and seismic resistance up to NEBS GR-63-CORE Bellcore zone 4 and industry leading radio-frequency/electromagnetic (RFI / EMI) shielding of 60 dB at 1 GHz, 40 dB at 3 GHz (tested to IEC 61587-3).

FUNKCJE

Type of protection IP 20

With glass front door

Doors with single point locking, side panels with quick release fastener

Static load-carrying capacity 1600 kg

OKREŚLENIU SPECYFIKACJI

Table 1/3

Numer katalogowy	Rack Height	Wysokość	Frame Color	Szerokość	Frame Color Code	Cladding Material
10630-038	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Stal
10630-037	38 U	1800 mm	Black Grey	600 mm	RAL 7021	Stal
10630-039	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Stal
10630-040	42 U	2000 mm	Black Grey	600 mm	RAL 7021	Stal

Table 2/3

Numer katalogowy	Głębokość	Cladding Color	Cladding Color Code	Zgodność z	Frame Material	Product Type
------------------	-----------	----------------	---------------------	------------	----------------	--------------

10630-038	800 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Stal	Cabinet
10630-037	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Stal	Cabinet
10630-039	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Stal	Cabinet
10630-040	600 mm	Black Grey	RAL 7021	IEC 60529, IEC 61587-1, IEC 60297-3-100, IEC 61587-1	Stal	Cabinet

Table 3/3

Numer katalogowy	Protection Rating	Obciążenie statyczne
10630-038	IP20	1600 kgf
10630-037	IP20	1600 kgf
10630-039	IP20	1600 kgf
10630-040	IP20	1600 kgf

ADDITIONAL PRODUCT DETAILS

Lever handle can be added to the doors.

Further dimensions and version available on ServicePlus EMC. Please order base/plinth separately. For assembly of shelves and slide rails another pair of panel/slide mounts is necessary.

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE