

NGC-40 Series, Power Distribution and Supply Panel

nVent RAYCHEM NGC-40 Panel Solution is a multipoint electronic control, monitoring and power distribution system with a unique single-point controller architecture, providing the most reliable central control and monitoring solution for your heat management system. Supporting up to 32 circuits per panel, the system offers fully flexible configuration and individual single-phase and three-phase controllers with SIL2 safety temperature limiters. System status and faults are reported to the user, displayed on the nVent RAYCHEM Touch 1500 user interface or remotely using nVent RAYCHEM Supervisor software.

FUNKCJE

Easy to install, configure and operate

Extensive control, monitoring, alarm and power distribution capabilities

Modular, providing configuration and component flexibility: optimizing project specific needs and costs

Comprehensive communications, system status and faults are reported with messages and alarms: optimizing maintenance and recovery time

OKREŚLENIU SPECYFIKACJI

Main Switch Current Rating: 160 A

Voltage Rating: 240 V

Table 1/1

Numer katalogowy	Nazwa pozycji	Circuit Breaker Quantity	Circuit Breaker	Control Module	Touch 1500 Included
1244-014352	PSS-160A/10kA-PDS-40-12HTC/25A-2HTC3/40A-T	14	25 A, Type C	12 x NGC-40-HTC, 2 x NGC-40-HTC3	Tak
1244-014353	PSS-160A/10KA-PDS-40-12HTC/25A-2HTC3/40A	14	25 A, Type C	12 x NGC-40-HTC, 2 x NGC-40-HTC3	Nie

Numer katalogowy	Nazwa pozycji	Circuit Breaker Quantity	Circuit Breaker	Control Module	Touch 1500 Included
1244-014348	PSS-160A/10KA-PDS-40-24HTC/16A-T	24	16 A, Type C	24 x NGC-40-HTC	Tak
1244-014349	PSS-160A/10KA-PDS-40-24HTC/16A	24	16 A, Type C	24 x NGC-40-HTC	Nie
1244-014350	PSS-160A/10KA-PDS-40-30HTC/16A-T	30	16 A, Type C	30 x NGC-40-HTC	Tak
1244-014351	PSS-160A/10KA-PDS-40-30HTC/16A	30	16 A, Type C	30 x NGC-40-HTC	Nie

OSTRZEŻENIE

Produkty nVent powinny być instalowane i używane wyłącznie zgodnie z instrukcjami i materiałami szkoleniowymi nVent. Instrukcje są dostępne na stronie www.nvent.com oraz u przedstawiciela działu obsługi klienta firmy nVent. Nieprawidłowa instalacja, niewłaściwe użycie, niewłaściwe zastosowanie lub inne nieprzestrzeganie instrukcji i ostrzeżeń nVent może spowodować nieprawidłowe działanie produktu, uszkodzenie mienia, poważne obrażenia ciała i śmierć i/lub utratę gwarancji.

Ameryka Północna

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

Europe, Middle East, Africa

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

Ameryka Łacińska

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT