

Motion detector

Data Solutions



Motion detector: Prepared for mounting on door box, detection method: movement, detection fields of radar are adjustable, wide field 4 m (W) x 2 m (D), narrow field 2 m (W) x 2.5 m (D), supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate.

CERTIFICATIONS



CARACTERISTICAS

Supply voltage 12 ... 24 VAC or 12 ... 30 VDC, power supply via connector on door plate

Wide field 4 m (W) x 2 m (D)

Arrow field 2 m (W) x 2.5 m (D)

Detection method: movement

Prepared for mounting on door box

Detection fields of radar are adjustable

ESPECIFICAÇÕES

Table 1/1

Número de catálogo	Tipo	Works With	Quantidade por embalagem
60130-067	Motion Detector	Aisle Containment	1

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE