

nVent CADDY Cat HP J-Hook with Pedestal Clamp

Data Solutions



CERTIFICATIONS



CARACTERÍSTICAS

Easy installation to pedestals used under raised floors

Provides optimal support for high-performance data cable, up to and including Cat 5e, Cat 6, Cat 6A, Cat 7 and fibre optic

Provides superior fill capacity and load rating over most other non-continuous cable support alternatives

Cost effective alternative to expensive cable tray

Complies with EN 50174-2

Meets ISO®/IEC 14763-2, ANSI®/TIA 568 and ANSI®/TIA 569

ESPECIFICAÇÕES

Acabamento: Pregalvanized

Material: Aço

Table 1/2

Número de catálogo	Número do artigo	Diâmetro (Ø)	Area	Cable Capacity, Cat 5e	Cable Capacity, Cat 6	Cable Capacity, Cat 6A
CAT32HPCD1B	181227	50mm	2561mm ²	90	60	35
CAT48HPCD1B	181228	75mm	5974mm ²	200	150	80
CAT64HPCD1B	181229	100mm	9987mm ²	330	220	140

Table 2/2


Número de catálogo	Número do artigo	Pedestal Size
CAT32HPCD1B	181227	19 mm Square, 22.2 - 28.5 mm Round
CAT48HPCD1B	181228	19 mm Square, 22.2 - 28.5 mm Round
CAT64HPCD1B	181229	19 mm Square, 22.2 - 28.5 mm Round

DETALHES ADICIONAIS DO PRODUTO

Non-continuous supports may not exceed spacing of 5' (1.5 m) per TIA 569-C.9.7 and EN 50174-2.

Cable capacity is calculated based on a 70% fill rate.

DIAGRAMAS



AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE