

19" Fan Unit, 1 U, Speed Control and Monitoring

Concessionárias de energia

Fan Unit for installation into a 1 U space within the Cabinet.



CERTIFICAÇÕES



RECURSOS

Range selectable: 20 ... 40 °C and 30 ... 50 °C

Low noise through temperature dependent air flow

External sensor, max speed is default failure state

Function control with LEDs and via dry contact

Contact protection in accordance with DIN EN ISO 13857

ESPECIFICAÇÕES

Table 1/1

Número do catálogo	Input Voltage AC	Input Voltage DC	Certificações
10713-098		24 V min	RoHS, CE, EAC
10713-099		24 V min	RoHS, CE, EAC

Número do catálogo	Input Voltage AC	Input Voltage DC	Certificações
19713-006	230 V min		RoHS, EAC
19713-121	230 V min		RoHS, EAC

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE