

Front Panel, Front Anodized, Rear Conductive, Shielded, Side Hinged, 3 U, 84 HP

Power Utilities

NÚMERO DE CATÁLOGO

20848-611



Front panel with textile EMC gasket, side hinged assembly.

CERTIFICATIONS



CARACTERÍSTICAS

Front panel with textile EMC gasket

Enables mounting onto the horizontal rails

Suitable for subracks and cases

Hinges can be fitted on left or right

CARACTERÍSTICAS DO PRODUTO

Product Type: Front Panel

Tipo: Front Panel without Handle

Instalação: Hinged, Side

EMC Shielding: No (Retrofittable)

Gasket Type: Textile

Material: Alumínio

Front Finish: Anodized

Rear Finish: Conductive

Treated Edges: Não

Rack Height: 3 U

Altura: 128.4 mm

Rack Width: 84 HP

Largura: 426.4 mm

Quantidade por embalagem: 1

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



O nosso forte portefólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE