


EuropacPRO 19" Subrack Kit for Backplane, Heavy, Shielded

Concessionárias de energia

EMC Shielded subrack for backplane mounting, heavy version with tox welded side panels.



CERTIFICAÇÕES



RECURSOS

Subrack with side panel type H ("Heavy"), 19" bracket is firmly fixed to side panel (tox-cold welded)

Modifications such as cutouts, different finishes or dimensions available

Supplied as space-saving flat-pack

Aluminum construction

Horizontal rail type "Heavy"

Rear horizontal rail for backplane mounting with insulation strip

EMC of approximately 40 dB at 1 GHz, 30 dB at 2 GHz, assuming that the front is covered with shielded front panels, testing in accordance with VG 95373 part 15

Internal and external dimensions in accordance with: IEC 60297-3-100, -101, IEEE 1101.1

Shock and vibration tested to the German "Bahn" standards BN 411002, BN 411003

IP 20, in accordance with IEC 60529

ESPECIFICAÇÕES

Table 1/3

Número do catálogo	Rack Height	Profundidade	Package Quantity	For Mounting	Board Depth	EMC Gasket Type
24563-172	3 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-173	3 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-174	3 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-472	6 U	235 mm	1	Backplane	160 mm, 220 mm	Textile
24563-473	6 U	295 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile
24563-474	6 U	355 mm	1	Backplane	160 mm, 220 mm, 280 mm	Textile

Table 2/3

Número do catálogo	Shock and Vibration Tolerance	Handle Included	Instalação	Em conformidade com	EMC Shielding	Product Type
24563-172	5 g (force)	Não	Rack	IEC 60297-3-103	Sim	Subrack/Chassis
24563-173	5 g (force)	Não	Rack	IEC 60297-3-103	Sim	Subrack/Chassis
24563-174	5 g (force)	Não	Rack	IEC 60297-3-103	Sim	Subrack/Chassis
24563-472	5 g (force)	Não	Rack	IEC 60297-3-103	Sim	Subrack/Chassis
24563-473	5 g (force)	Não	Rack	IEC 60297-3-103	Sim	Subrack/Chassis
24563-474	5 g (force)	Não	Rack	IEC 60297-3-103	Sim	Subrack/Chassis

Table 3/3

Número do catálogo	Rack Width	Carga estática
24563-172	84 HP	15 kgf
24563-173	84 HP	15 kgf

Número do catálogo	Rack Width	Carga estática
24563-174	84 HP	15 kgf
24563-472	84 HP	15 kgf
24563-473	84 HP	15 kgf
24563-474	84 HP	15 kgf

ADDITIONAL PRODUCT DETAILS

Individual configuration: broad range of variants in height, width and depth; guide rails for a wide variety of applications; interior options; accessories and mounting material.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE