

Front Panel, Anodized, Unshielded, Screw Assembly

Concessionárias de energia

Anodized front panel, unshielded version, Al, 2.5 mm.



CERTIFICAÇÕES



RECURSOS

Partial width front panel, Al, 2.5 mm

Al, anodized

ESPECIFICAÇÕES

Table 1/3

Número do catálogo	Rack Height	Rack Width	Package Quantity	Instalação	Front Finish	Rear Finish
30807-416	2 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-494	3 U	42 HP	1	Screw-on Front	Anodized	Anodized

Número do catálogo	Rack Height	Rack Width	Package Quantity	Instalação	Front Finish	Rear Finish
30807-506	3 U	84 HP	1	Screw-on Front	Anodized	Anodized
30807-764	6 U	42 HP	1	Screw-on Front	Anodized	Anodized
30807-771	6 U	63 HP	1	Screw-on Front	Anodized	Anodized
30807-776	6 U	84 HP	1	Screw-on Front	Anodized	Anodized
30808-067	3 U	63 HP	1	Screw-on Front	Anodized	Anodized
30810-432	3 U	2 HP	5	Screw-on Front	Anodized	Anodized
30818-741	6 U	2 HP	5	Screw-on Front	Anodized	Conductive
30807-481	3 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-482	3 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-483	3 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-484	3 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-485	3 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-487	3 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-496	3 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-501	3 U	14 HP	5	Screw-on Front	Anodized	Anodized
30807-508	3 U	3 HP	5	Screw-on Front	Anodized	Anodized
30807-509	3 U	7 HP	5	Screw-on Front	Anodized	Anodized
30807-510	3 U	5 HP	5	Screw-on Front	Anodized	Anodized

Número do catálogo	Rack Height	Rack Width	Package Quantity	Instalação	Front Finish	Rear Finish
30807-778	6 U	4 HP	5	Screw-on Front	Anodized	Anodized
30807-777	6 U	5 HP	5	Screw-on Front	Anodized	Anodized
30807-752	6 U	6 HP	5	Screw-on Front	Anodized	Anodized
30807-753	6 U	10 HP	5	Screw-on Front	Anodized	Anodized
30807-755	6 U	12 HP	5	Screw-on Front	Anodized	Anodized
30807-757	6 U	21 HP	5	Screw-on Front	Anodized	Anodized
30807-758	6 U	14 HP	5	Screw-on Front	Anodized	Conductive
30807-766	6 U	28 HP	5	Screw-on Front	Anodized	Anodized
30807-779	6 U	8 HP	5	Screw-on Front	Anodized	Anodized
30807-780	6 U	16 HP	5	Screw-on Front	Anodized	Anodized

Table 2/3

Número do catálogo	Treated Edges	Em conformidade com	EMC Shielding	Altura	Material	Product Type
30807-416	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	84 mm	Alumínio	Front Panel
30807-494	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-506	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-764	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-771	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel

Número do catálogo	Treated Edges	Em conformidade com	EMC Shielding	Altura	Material	Product Type
30807-776	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30808-067	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30810-432	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30818-741	Não	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-481	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-482	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-483	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-484	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-485	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-487	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-496	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-501	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-508	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-509	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel

Número do catálogo	Treated Edges	Em conformidade com	EMC Shielding	Altura	Material	Product Type
30807-510	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	128.4 mm	Alumínio	Front Panel
30807-778	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-777	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-752	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-753	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-755	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-757	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-758	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-766	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-779	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel
30807-780	Sim	IEC 60297-3-101, IEEE 1101.1/10	Não	261.8 mm	Alumínio	Front Panel

Table 3/3

Número do catálogo	Tipo	Largura
30807-416	Front Panel without Handle	426.4 mm
30807-494	Front Panel without Handle	213 mm
30807-506	Front Panel without Handle	426.4 mm

Número do catálogo	Tipo	Largura
30807-764	Front Panel without Handle	213 mm
30807-771	Front Panel without Handle	319.7 mm
30807-776	Front Panel without Handle	426.4 mm
30808-067	Front Panel without Handle	319.7 mm
30810-432	Front Panel without Handle	9.8 mm
30818-741	Front Panel without Handle	9.8 mm
30807-481	Front Panel without Handle	20 mm
30807-482	Front Panel without Handle	30.1 mm
30807-483	Front Panel without Handle	50.5 mm
30807-484	Front Panel without Handle	40.3 mm
30807-485	Front Panel without Handle	60.6 mm
30807-487	Front Panel without Handle	106.3 mm
30807-496	Front Panel without Handle	141.9 mm
30807-501	Front Panel without Handle	70.8 mm
30807-508	Front Panel without Handle	14.9 mm
30807-509	Front Panel without Handle	35.2 mm
30807-510	Front Panel without Handle	25 mm
30807-778	Front Panel without Handle	20 mm

Número do catálogo	Tipo	Largura
30807-777	Front Panel without Handle	25 mm
30807-752	Front Panel without Handle	30.1 mm
30807-753	Front Panel without Handle	50.5 mm
30807-755	Front Panel without Handle	60.6 mm
30807-757	Front Panel without Handle	106.3 mm
30807-758	Front Panel without Handle	70.8 mm
30807-766	Front Panel without Handle	141.9 mm
30807-779	Front Panel without Handle	40.3 mm
30807-780	Front Panel without Handle	80.9 mm

ADDITIONAL PRODUCT DETAILS

Please order fixing material (sleeves, collar screws) separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE