

Varistar CP Steel Door, Glazed With 3-Point Locking, Shortened

Concessionárias de energia

Shortened door available for IP20, IP55 applications.

RECURSOS

Glazed door

Height of connection plate 400mm

ESPECIFICAÇÕES

Table 1/2

Número do catálogo	Rack Height	Altura	Largura	Cor	Color Code	Locking Type
21630-342	38 U	1800 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-343	38 U	1800 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-344	42 U	2000 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-345	42 U	2000 mm	800 mm	Black Grey	RAL 7021	3-Point Locking
21630-346	47 U	2200 mm	600 mm	Black Grey	RAL 7021	3-Point Locking
21630-347	47 U	2200 mm	800 mm	Black Grey	RAL 7021	3-Point Locking

Table 2/2

Número do catálogo	Product Type	Protection Rating
21630-342	Cabinet Door	IP20

Número do catálogo	Product Type	Protection Rating
21630-343	Cabinet Door	IP20
21630-344	Cabinet Door	IP20
21630-345	Cabinet Door	IP20
21630-346	Cabinet Door	IP20
21630-347	Cabinet Door	IP20

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.



Our powerful portfolio of brands:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE