

920 Series, Solid-State Relay



RAYCHEM 920 Series - SSR provides electronic switching capability for heat trace circuits. Available in 1-,2-, or 3-pole solid-state, normally open relay , 277V or 600V, and 30A or 60A at 104°F (40°C). Allows for proportional, power limiting, and soft start control algorithms.

RECURSOS

Fácil de instalar

Suitable for Class I Div. 2/Zone 2 hazardous locations

Infinite Life Cycle

ESPECIFICAÇÕES

Table 1/1

Número do catálogo	Nome do item	Voltage Rating	Current Rating
10260-008	SS3	277 V max	30 A
10260-009	SSH3	600 V max	30 A
10260-011	SSH6	600 V max	60 A

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

América do Norte

Tel +1.800.545.6258

Fax +1.800.527.5703

thermal.info@nvent.com

**Europe, Middle East,
Africa**

Tel +32.16.213.511

Fax +32.16.213.604

thermal.info@nvent.com

Asia Pacific

Tel +86.21.2412.1688

Fax +86.21.5426.3167

cn.thermal.info@nvent.com

América Latina

Tel +1.713.868.4800

Fax +1.713.868.2333

thermal.info@nvent.com

Our powerful portfolio of brands:

RAYCHEM PYROTENAX TRACER NUHEAT