

Air Baffle, U-Front Panel, Refrofit Shielding, Textile



The air baffle with U-shaped front panel covers an empty slot to eliminate an air flow exit. The U-shaped front panel accepts a textile EMC gasket.

CERTIFICATIONS



CARACTERISTICAS

air baffle eliminates air leaks in empty slots

Cover is pushed into the guide rail

ESPECIFICAÇÕES

Product Type:	Air Baffle
Material:	Aluminio
Acabamento:	Anodized; Passivated
Família de produtos:	EuropacPRO; RatiopacPRO; RatiopacPRO AIR; CompacPRO; PropacPRO; Inpac
Tipo:	With Front Panel

Table 1/2

Número de catálogo	Rack Height	Quantidade por embalagem	Profundidade	EMC Shielding	Rack Width	Works With
20848-728	3U	1	160mm	No (Retrofittable)	4HP	Subracks, Cases

Número de catálogo	Rack Height	Quantidade por embalagem	Profundidade	EMC Shielding	Rack Width	Works With
20848-737	6U	1	220mm	No (Retrofittable)	4HP	Subracks, Cases
20848-736	6U	1	160mm	No (Retrofittable)	4HP	Subracks, Cases
20848-729	3U	1	220mm	No (Retrofittable)	4HP	Subracks, Cases

Table 2/2

Número de catálogo	Envio rápido
20848-728	Não
20848-737	Não
20848-736	Não
20848-729	Não

DETALHES ADICIONAIS DO PRODUTO

Air baffle for 280 mm deep and for 80 mm rear I/O boards available on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE