

Connection clamp with levers

Distribution Clamps for Distribution Box.



CARACTERISTICAS

Connection clamp with levers

For all conductor types

3 or 5 conductors

Up to 4.00 mm²

ESPECIFICAÇÕES

Table 1/3

Número de catálogo	Product Type	Cor	Temperatura ambiente	Clamp Quantity	Profundidade	Altura
20118-902	Clamp	Transparente, Green	85°C max	3	18.8mm	8.4mm
20118-903	Clamp	Transparente, Green	85°C max	5	18.8mm	8.4mm

Table 2/3

Número de catálogo	Material	Corrente máxima	Max Voltage	Quantidade por embalagem	Peso	Largura
20118-902	Polycarbonato	20A	600V	10	2.5g	18.8mm
20118-903	Polycarbonato	20A	600V	10	4g	30mm

Table 3/3

Número de catálogo	Envio rápido
--------------------	--------------

20118-902	Não
20118-903	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE