

CPCI Serial System With Pluggable PSU, 4 U, 9 Slot

4 U CompactPCI Serial System with vertical Card Cage for nine 3 U Boards and one 3U Pluggable Power Supply.



CERTIFICATIONS



CARACTERÍSTICAS

System in accordance with IEC 60297-3-101, -102, -103; IEEE 1101.1, 1101.10/11; backplane in accordance with PICMG CPCI-S.0

System with vertical card cage. For Board format 3U

Backplane 9 slot, 3U CompactPCI Serial (single star Ethernet topology), System slot left

Heat dissipation via 1 U hot-swap fan unit

Supports PCIe up to Gen3, USB 2.0 and 3.0, SATA up to Rev 3.0, and Ethernet up to 10 GBase-T

Retrofittable air filter

ESPECIFICAÇÕES

Table 1/3

Número de catálogo	Product Type	Number of Slots	Tipo	Backplane Type	Data Transfer	Power per Slot
24579-421	System	9	19" Rack Mount	3 U CompactPCI Serial with Ethernet Star	PCIe Gen3	40W

Número de catálogo	Product Type	Number of Slots	Tipo	Backplane Type	Data Transfer	Power per Slot
24579-416	System	9	19" Rack Mount	3 U CompactPCI Serial with Ethernet Star	PCIe Gen3	40W

Table 2/3

Número de catálogo	Tensão de entrada AC	Airflow Direction	Rack Height	Power Supply Type	Power Supply Included	Rear I/O
24579-421	100 – 240V	Bottom to Top	4U	(2) Pluggable PSU	Sim	Sim
24579-416	100 – 240V	Bottom to Top	4U	(1) Pluggable PSU	Sim	Não

Table 3/3

Número de catálogo	Em conformidade com	Profundidade	Altura	Quantidade por embalagem	Envio rápido
24579-421	PICMG CPCI-S.0 R2.0	275mm	177mm	1	Não
24579-416	PICMG CPCI-S.0 R2.0	275mm	177mm	1	Não

DETALHES ADICIONAIS DO PRODUTO

Preference types can be ordered directly from stock, other configurations on request.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE