

Intelligent iPDU, EN6450, 400 VAC, 3-PH, 16 A

NÚMERO DE CATÁLOGO

EN6450



Modular, compact intelligent PDU with inlet metering. Ultra-Low Profile Design

CARACTERÍSTICAS

Enlogic EN6xxx Intelligent Power Distribution Units monitors input power and power of each individual outlet and offers remote switching of individual outlets, provides billing grade unit level monitoring

High Visibility Data Display and Interactive Graphic Display

Measure circuit breaker loads across redundant feeds to avoid accidental downtime

Enables smart load balancing for power efficiency and maximized capacity utilization

Gigabit Ethernet Interface and redundant Ethernet (10/100)

iPDU DC power redundancy solution for up to 64 PDU's

Toolless Hot-Swap Controller

Input voltage 400 VAC, 3-phase

C13, C19 outlets

CARATERÍSTICAS DO PRODUTO

Família de produtos: Enlogic

Tipo: Intelligent PDU

Product Type: Socket Strip

Tipo de soquete: (24) C13/C15; (24) C13/C15/C19/C21

Socket Quantity: 48

Cor: Black

Circuit Breaker: No Circuit Breaker

Switched Outlets: Sim

Circuit Breaker Quantity: 0

Power Rating: 11.5 kVA North America; 11.0 kVA International

Input Cable Location: Top Feed

Max Power Input: 11.5 / 11.0 kVA

Input Voltage: 380 – 415V

Phase: 3 PH

On/Off Switch Included: Sim

Tensão nominal: 415V

Output Voltage: 208 – 230VAC

Plug Type: IEC 60309 520P6/516P6

Amperage (Derated Amperage): 20 A (16 A) North America; 16 A International

Removable Input Cable: Não

Rack Units: 0U

Material: Aço

Acabamento: Pintura electrostática com Acabamento Texturado

Metering Type: Outlet

Altura: 1490mm

Largura: 56mm

Profundidade: 75mm

Peso: 12kg

Quantidade por embalagem: 1

Input Cable Length: 1.8m

DETALHES ADICIONAIS DO PRODUTO

Please order bracket for vertical mounting separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY

ERICO

HOFFMAN

ILSCO

SCHROFF

TRACHTE