

EuropacPRO Rear Angle for Textile EMC Gasket



EuropacPro rear angle for Textile EMC Gasket, out of Aluminum extrusion with etched surface. Rear hood cannot be mounted simultaneously.

CERTIFICATIONS



CARACTERISTICAS

Required for rear shielding

Also useable at the front if you use a depth-adjustable 19" support bracket

ESPECIFICAÇÕES

Material:	Aluminio
Product Type:	Cover
Família de produtos:	EuropacPRO
Tipo:	Rear Angle
Works With:	Subracks

Table 1/1

Número de catálogo	Rack Height	Quantidade por embalagem	Altura	Unidade de embalagem	Envio rápido
24564-199	3U	2	132.6mm	Pair	Não
24564-799	9U	2	399.3mm	Pair	Não

Número de catálogo	Rack Height	Quantidade por embalagem	Altura	Unidade de embalagem	Envio rápido
24564-299	4U	2	177mm	Pair	Não
24564-499	6U	2	265.9mm	Pair	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE