

Interscale 19" Rack Mount Chassis, Non-Perforated

Flexible 19" Chassis with integrated EMC protection. Based on the nVent SCHROFF Interscale platform and developed in accordance with IEC 60297-3-109.



CERTIFICATIONS



CARACTERÍSTICAS

Modular desktop case consisting of 4 assembled parts

Developed according to IEC 60297-3-109 (under progress at IEC)

Integrated EMC protection

Ingress protection up to IP 30

Color RAL 7016

Modified or customized cases available upon request

ESPECIFICAÇÕES

Material:	Aço; Alumínio
Família de produtos:	Interscale
Product Type:	Small Form Factor Case
Tipo:	Solid
EMC Shielding:	Sim

Table 1/2

Número de catálogo	Rack Height	Profundidade	Quantidade por embalagem	Usable Width	Instalação	Em conformidade com
14821-105	1U	221.45mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-107	1U	310.35mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-307	3U	310.35mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-305	3U	221.45mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-207	2U	310.35mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109
14821-205	2U	221.45mm	1	443.7mm	Rack	IEC 60297-3-100, IEC 60297-3-109

Table 2/2

Número de catálogo	Acabamento	Envio rápido
14821-105	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado	Não
14821-107	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado	Não
14821-307	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado	Não
14821-305	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado	Não
14821-207	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado	Não
14821-205	Aluminum-Zinc Plated, Pintura electrostática com Acabamento Texturado	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE