


MultipacPRO 19" Chassis, Aluminum, for Eurocards Assembly



This 19" chassis is a form of subrack which accepts horizontal board mounting or the mounting of non-standard components like transformers or other heavy load accessories typically mounted on a chassis plate. This version are prepared for horizontal PCB board assembly.

CERTIFICATIONS



CARACTERÍSTICAS

Aluminum construction

Detachable front and rear panel for easy machining

IP 20, in accordance with IEC 60529

Supplied as space-saving flat-pack

Modifications such as cutouts, different finishes or dimensions available

Internal and external dimensions in accordance with: IEC 60297-3-100, -105

EMC shielding: Approx. 20dB(A) at 2 GHz without shielding material. >40dB(A) at 1 GHz with addition of stainless steel gasket between front panel and case body

Cover and base plate drilled with holes for horizontal mounting of euroboards

ESPECIFICAÇÕES

Material:	Aluminio
Acabamento:	Anodized; Passivated
Família de produtos:	MultipacPRO
EMC Shielding:	No (Retrofittable)

Tipo: Solid
Product Type: Subrack/Chassis

Table 1/1						
Número de catálogo	Rack Height	Profundidade	Usable Width	Instalação	Em conformidade com	Envio rápido
20860-641	1U	220mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-101, IEC 60297-3-105	Não
20860-642	1U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-101, IEC 60297-3-105	Não
20860-645	2U	280mm	403mm	Rack	IEC 60297-3-100, IEC 60297-3-101	Não

DETALHES ADICIONAIS DO PRODUTO

Please order front handles separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE