

PMC Mezzanine Front Panel, Untreated, With EMC Shielding



Mezzanine front panel is fitted into PMC front panel cut-outs. Available in different treatments. For O-ring EMC gasket.

CERTIFICATIONS



CARACTERÍSTICAS

Mezzanine front panel is fitted into PMC front panel cut-outs

EMC shielding with conductive O-ring

ESPECIFICAÇÕES

Product Type:	Front Panel
Tipo:	Front Panel without Handle
EMC Shielding:	Sim

Table 1/3

Número de catálogo	Quantidade por embalagem	Accessory Type	Instalação	Gasket Type	Front Finish	Rear Finish
20835-598	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-890	1		Screw-on Front			

Número de catálogo	Quantidade por embalagem	AccessoryType	Instalação	Gasket Type	Front Finish	Rear Finish
20835-923	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-922	1		Screw-on Front		Chrome Plated	Chrome Plated
20835-889	1	Front panel	Screw-on Front	O-Ring EMC	Anodized	Conductive
20835-924	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-893	10		Screw-on Front		Chrome Plated	Chrome Plated
20835-928	10		Screw-on Front		Anodized	Conductive

Table 2/3						
Número de catálogo	Treated Edges	Em conformidade com	Profundidade	Acabamento	Altura	Material
20835-598	Não	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Aluminio
20835-890	Não	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-923	Sim	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-922	Sim	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-889	Não	PMC Mezzanine, IEEE P1386	2.5mm	Anodized	74mm	Aluminio
20835-924	Sim	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-893	Sim	PMC Mezzanine, IEEE P1386			74mm	Zinc
20835-928	Não	PMC Mezzanine, IEEE P1386			74mm	Zinc

Table 3/3

Número de catálogo	Largura	Envio rápido
20835-598	12.7mm	Não
20835-890	12.7mm	Não
20835-923	12.7mm	Não
20835-922	12.7mm	Não
20835-889	12.7mm	Não
20835-924	12.7mm	Não
20835-893	12.7mm	Não
20835-928	12.7mm	Não

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE