

PSU 19" AC/DC Linear Regulator, Dual

Linear regulator for application which only allows a very low noise level at the outputs.



CERTIFICATIONS



CARACTERÍSTICAS

2 output voltages, galvanically separated

High control accuracy, low residual ripple and very low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

ESPECIFICAÇÕES

Table 1/3

Número de catálogo	Tipo	Tensão de entrada AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-018	19" Linear Regulator	230V	12W	2	15V	0.4A
13105-017	19" Linear Regulator	230V	10W	2	12V	0.4A
13105-022	19" Linear Regulator	230V	24W	2	12V	1A

Número de catálogo	Tipo	Tensão de entrada AC	Power	Number of Output Voltages	Voltage 1	Current 1
13105-023	19" Linear Regulator	230V	30W	2	15V	1A
13105-029	19" Linear Regulator	230V	58W	2	24V	1.2A
13105-028	19" Linear Regulator	230V	45W	2	15V	1.5A
13105-021	19" Linear Regulator	230V	14W	2	5V	1.4A
13105-027	19" Linear Regulator	230V	36W	2	12V	1.5A

Table 2/3

Número de catálogo	Voltage 2	Current 2	Rack Height	Rack Width	Profundidade	Quantidade por embalagem
13105-018	15V	0.4A	3U	6HP	171.93mm	1
13105-017	12V	0.4A	3U	6HP	171.93mm	1
13105-022	12V	1A	3U	10HP	171.93mm	1
13105-023	15V	1A	3U	10HP	171.93mm	1
13105-029	24V	1.2A	3U	14HP	171.93mm	1
13105-028	15V	1.5A	3U	14HP	171.93mm	1
13105-021	5V	1.4A	3U	10HP	171.93mm	1
13105-027	12V	1.5A	3U	14HP	171.93mm	1

Table 3/3

Número de catálogo	Certifications	Envio rápido
13105-018	EN 62368-1, RoHS, CE	Não
13105-017	EN 62368-1, RoHS, CE	Não

Número de catálogo	Certifications	Envio rápido
13105-022	CE, RoHS	Não
13105-023	CE, RoHS	Não
13105-029	CE, RoHS	Não
13105-028	RoHS, CE	Não
13105-021	RoHS, CE	Não
13105-027	RoHS, CE	Não

DETALHES ADICIONAIS DO PRODUTO

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE