

# PSU 19" AC/DC Linear Regulator, Triple

Linear regulator for applications requiring very low output noise level.



## CERTIFICATIONS



## CARACTERÍSTICAS

3 output voltages, galvanically separated

High control accuracy, low residual ripple and very low interference

Mains/line voltage 230 VAC (can be switched to 115 VAC with mains/line voltage conversion kit)

Suited for medical applications (8 mm safety clearances)

## ESPECIFICAÇÕES

Table 1/3

| Número de catálogo | Tipo                 | Tensão de entrada AC | Power | Number of Output Voltages | Voltage 1 | Current 1 |
|--------------------|----------------------|----------------------|-------|---------------------------|-----------|-----------|
| 13105-051          | 19" Linear Regulator | 230V                 | 8W    | 3                         | 5V        | 0.5A      |
| 13105-052          | 19" Linear Regulator | 230V                 | 20W   | 3                         | 5V        | 1.5A      |
| 13105-053          | 19" Linear Regulator | 230V                 | 39W   | 3                         | 5V        | 3A        |

Table 2/3

| Número de catálogo | Voltage 2 | Current 2 | Voltage 3 | Current 3 | Rack Height | Rack Width |
|--------------------|-----------|-----------|-----------|-----------|-------------|------------|
| 13105-051          | 12V       | 0.2A      | 12V       | 0.2A      | 3U          | 6HP        |
| 13105-052          | 12V       | 0.5A      | 12V       | 0.5A      | 3U          | 10HP       |
| 13105-053          | 12V       | 1A        | 12V       | 1A        | 3U          | 14HP       |

Table 3/3

| Número de catálogo | Profundidade | Quantidade por embalagem | Certifications       | Envio rápido |
|--------------------|--------------|--------------------------|----------------------|--------------|
| 13105-051          | 171.93mm     | 1                        | RoHS, CE, EN 62368-1 | Não          |
| 13105-052          | 171.93mm     | 1                        | CE, RoHS             | Não          |
| 13105-053          | 171.93mm     | 1                        | RoHS, CE             | Não          |

## DETALHES ADICIONAIS DO PRODUTO

Please order Front Panel separately.

Output Data at Ta= 0 ... 50 °C.

## AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em [www.nVent.com](http://www.nVent.com) e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

### North America

All locations  
+1.763.422.2661  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Europe

Straubenhardt, Germany  
+49.7082.794.0  
Betschdorf, France  
+33.3.88.90.64.90  
Warsaw, Poland  
+48.22.209.98.35  
Assago, Italy  
+39.02.932.7141  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Asia

Shanghai, China  
+86.21.2412.6943  
Qingdao, China  
+86.532.8771.6101  
Singapore  
+65.6768.5800  
Shin-Yokohama, Japan  
+81.45.476.0271  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)

### Middle East & India

Dubai, United Arab Emirates  
+971.4.378.1700  
Bangalore, India  
+91.80.6715.2001  
Istanbul, Turkey  
+90.216.250.7374  
Chat with us:  
[nvent.com/schroff](https://nvent.com/schroff)



O nosso forte portfólio de marcas:

**CADDY**

**ERICO**

**HOFFMAN**

**ILSCO**

**SCHROFF**

**TRACHTE**