

PSU 19" AC/DC Maxpower 100 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications. With wide range AC input and one output voltage.

CERTIFICATIONS



CARACTERISTICAS

Wide input voltage range 90 ... 254 VAC and 100 ... 360 VDC with active power factor correction (PFC)

1 output voltage

Signalling: Output voltage OK

High power density

Integrated decoupling diode for redundancy operation

Active Current Share Bus (CSB)

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Tipo	Tensão de entrada AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-105	19" Switched-Mode	90 – 264V	101W	1	24V	4.2A
13100-103	19" Switched-Mode	90 – 264V	100W	1	12V	8.3A

Número de catálogo	Tipo	Tensão de entrada AC	Power	Number of Output Voltages	Voltage 1	Current 1
13100-104	19" Switched-Mode	90 – 264V	99W	1	15V	6.6A
13100-102	19" Switched-Mode	90 – 264V	80W	1	5V	16A

Table 2/2

Número de catálogo	Rack Height	Rack Width	Quantidade por embalagem	Envio rápido
13100-105	3U	6HP	1	Não
13100-103	3U	6HP	1	Não
13100-104	3U	6HP	1	Não
13100-102	3U	6HP	1	Não

DETALHES ADICIONAIS DO PRODUTO

Please order front panel separately.

Output data at mains voltage > 190 VAC, $T_a = 0 \dots 50 \text{ }^{\circ}\text{C}$.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE