

PSU 19" AC/DC for VMEbus



Pluggable 19" Power Supply for VMEbus applications.

CERTIFICATIONS



CARACTERISTICAS

Wide input voltage range 90 ... 264 VAC and 130 ... 350 VDC with active power factor correction (PFC)

VMEbus signalling

3 output voltages

ESPECIFICAÇÕES

Table 1/3

Número de catálogo	Tipo	Works With	Tensão de entrada AC	Power	Number of Output Voltages	Voltage 1
13100-205	19" Switched-Mode	VMEbus Systems	90 – 264V	150W	3	5V
13100-203	19" Switched-Mode	VMEbus Systems	90 – 264V	224W	3	5V
13100-204	19" Switched-Mode	VMEbus Systems	90 – 264V	224W	3	5V

Table 2/3

Número de catálogo	Current 1	Voltage 2	Current 2	Voltage 3	Current 3	Rack Height
13100-205	20A	12V	4A	-12V	3A	6U
13100-203	28A	12V	7A	-12V	3A	6U
13100-204	28A	15V	5.6A	-15V	2.4A	6U

Table 3/3

Número de catálogo	Rack Width	Profundidade	Quantidade por embalagem	Envio rápido
13100-205	8HP	171.93mm	1	Não
13100-203	12HP	171.93mm	1	Não
13100-204	12HP	171.93mm	1	Não

DETALHES ADICIONAIS DO PRODUTO

Output data at TU = 0 ... 40 °C.

Output power V2 + V3 = 60 W.

Output currents (UL values in bracket): V1 = 5 V / I1 = 20 A (18 A) V2 = 12 V / I2 = 4 A (3 A) V3 = -12 V / I3 = 3 A (2 A).

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab
Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portfólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE