

PSU 19" DC/DC Coolpower 100 W, Single



Pluggable 19" Power Supplies with H15 connector for fanless applications.

CERTIFICATIONS



CARACTERÍSTICAS

Wide input voltage range from 20 to 72 VDC

Galvanic separation between primary and secondary circuits

High power density

External ON/OFF

ESPECIFICAÇÕES

Table 1/2

Número de catálogo	Tipo	Tensão de entrada DC	Power	Number of Output Voltages	Voltage 1	Current 1
13103-003	19" DC/DC Converter	20 – 72V	102W	1	12V	8.5A
13103-004	19" DC/DC Converter	20 – 72V	100W	1	15V	6.7A
13103-002	19" DC/DC Converter	20 – 72V	100W	1	5V	20A

Table 2/2

Número de catálogo	Rack Height	Rack Width	Profundidade	Quantidade por embalagem	Envio rápido
13103-003	3U	6HP	171.93mm	1	Não
13103-004	3U	6HP	171.93mm	1	Não
13103-002	3U	6HP	171.93mm	1	Não

DETALHES ADICIONAIS DO PRODUTO

Please order front panel separately.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE