

RatiopacPRO 19" Rack Mount Case, Retrofittable Shielding With Handles



The nVent SCHROFF RatiopacPRO case provides electronics protection for 19" and individual electronic assemblies. This flexible and robust case is simple to convert from desktop to a 19" rack mount case and includes four different style options. This version of the case provides mounting brackets and handles for assembly into a 19" rack.

CERTIFICATIONS



CARACTERÍSTICAS

Cases for individual assembly with 19" standard components or specific internal mounting, e.g. with mounting plate

Designed for insertion/extractor handles in accordance with IEC 60297-3-102 and IEEE 1101.10 for CompactPCI and VME64x applications

Version with 19" mounting brackets with front handles

Retrofittable EMC shielding

For board depth 160 mm, 220 mm, 280 mm, and 340 mm (depending on case depth)

No visible screws; cladding parts removable without tools

Symmetrical design, identical front and rear side

Conforms with DIN EN 62368-1

ESPECIFICAÇÕES

Rack Width:	84HP
Product Type:	Case
Tipo:	Case for Individual Electronic Components
EMC Shielding:	No (Retrofittable)

Table 1/3

Número de catálogo	Rack Height	Profundidade	Quantidade por embalagem	Usable Height	Usable Width	Front Frame Construction
24572-620	2U	255.5mm	1	67.9mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-623	2U	315.5mm	1	67.9mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-624	2U	375.5mm	1	67.9mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-625	2U	435.5mm	1	67.9mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-626	2U	495.5mm	1	67.9mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-630	3U	255.5mm	1	112.3mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-633	3U	315.5mm	1	112.3mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-634	3U	375.5mm	1	112.3mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-635	3U	435.5mm	1	112.3mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-636	3U	495.5mm	1	112.3mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails

Número de catálogo	Rack Height	Profundidade	Quantidade por embalagem	Usable Height	Usable Width	Front Frame Construction
24572-640	4U	255.5mm	1	156.8mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-643	4U	315.5mm	1	156.8mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-644	4U	375.5mm	1	156.8mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-645	4U	435.5mm	1	156.8mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-646	4U	495.5mm	1	156.8mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-660	6U	255.5mm	1	245.7mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-663	6U	315.5mm	1	245.7mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-664	6U	375.5mm	1	245.7mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-665	6U	435.5mm	1	245.7mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails
24572-666	6U	495.5mm	1	245.7mm	432mm	19" Mounting Brackets with Handles, Horizontal Rails

Table 2/3

Número de catálogo	Cooling Option	Em conformidade com	Acabamento	Altura	Material	Grau de proteção
--------------------	----------------	---------------------	------------	--------	----------	------------------

24572-620	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	88.1mm	Aluminio	IP20
24572-623	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	88.1mm	Aluminio	IP20
24572-624	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	88.1mm	Aluminio	IP20
24572-625	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	88.1mm	Aluminio	IP20
24572-626	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	88.1mm	Aluminio	IP20
24572-630	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	132.6mm	Aluminio	IP20
24572-633	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	132.6mm	Aluminio	IP20
24572-634	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	132.6mm	Aluminio	IP20

24572-635	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	132.6mm	Aluminio	IP20
24572-636	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	132.6mm	Aluminio	IP20
24572-640	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	177mm	Aluminio	IP20
24572-643	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	177mm	Aluminio	IP20
24572-644	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	177mm	Aluminio	IP20
24572-645	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	177mm	Aluminio	IP20
24572-646	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	177mm	Aluminio	IP20
24572-660	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	265.9mm	Aluminio	IP20

24572-663	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	265.9mm	Aluminio	IP20
24572-664	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	265.9mm	Aluminio	IP20
24572-665	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	265.9mm	Aluminio	IP20
24572-666	Não	IEC 60297-3-101, IEC 60297-3-102, IEEE 1101.1, IEEE 1101.10, IEEE 1101.11	Passivated, Pintura electrostática com Acabamento Texturado	265.9mm	Aluminio	IP20

Table 3/3

Número de catálogo	Static Load	Largura	Envio rápido
24572-620	25kg	448.9mm	Não
24572-623	25kg	448.9mm	Não
24572-624	25kg	448.9mm	Não
24572-625	25kg	448.9mm	Não
24572-626	25kg	448.9mm	Não
24572-630	25kg	448.9mm	Não
24572-633	25kg	448.9mm	Não
24572-634	25kg	448.9mm	Não

Número de catálogo	Static Load	Largura	Envio rápido
24572-635	25kg	448.9mm	Não
24572-636	25kg	448.9mm	Não
24572-640	25kg	448.9mm	Não
24572-643	25kg	448.9mm	Não
24572-644	25kg	448.9mm	Não
24572-645	25kg	448.9mm	Não
24572-646	25kg	448.9mm	Não
24572-660	25kg	448.9mm	Não
24572-663	25kg	448.9mm	Não
24572-664	25kg	448.9mm	Não
24572-665	25kg	448.9mm	Não
24572-666	25kg	448.9mm	Não

DETALHES ADICIONAIS DO PRODUTO

Modifications (special colours or sizes).

Custom solutions (cut-outs in top cover, base plate or side panels).

Assembly service from 1 piece.

AVISO

Os produtos nVent devem ser instalados e utilizados apenas conforme indicado nas fichas de instrução do produto e materiais de treinamento da nVent. As fichas de instrução estão disponíveis em www.nVent.com e com nossos representantes de atendimento ao cliente nVent. A instalação inadequada, uso incorreto, aplicação incorreta ou outra falha qualquer em seguir completamente as instruções e avisos da nVent podem levar ao mau funcionamento do produto, danos à propriedade, lesões corporais graves e morte, e/ou anular sua garantia.

North America

All locations
+1.763.422.2661
Chat with us:
nvent.com/schroff

Europe

Straubenhardt, Germany
+49.7082.794.0
Betschdorf, France
+33.3.88.90.64.90
Warsaw, Poland
+48.22.209.98.35
Assago, Italy
+39.02.932.7141
Chat with us:
nvent.com/schroff

Asia

Shanghai, China
+86.21.2412.6943
Qingdao, China
+86.532.8771.6101
Singapore
+65.6768.5800
Shin-Yokohama, Japan
+81.45.476.0271
Chat with us:
nvent.com/schroff

Middle East & India

Dubai, United Arab Emirates
+971.4.378.1700
Bangalore, India
+91.80.6715.2001
Istanbul, Turkey
+90.216.250.7374
Chat with us:
nvent.com/schroff



O nosso forte portefólio de marcas:

CADDY ERICO HOFFMAN ILSCO SCHROFF TRACHTE